



OBJECTS AND PASSION LEA
 O FARMS
 USTRY THIS IS OUR
 RTNER IN THE LARGEST TELECO
 LEADING TECHNOLOGY
 RIVING BUSINESS IN THE RENewa
 PROJECT IN AUSTRALIA'S HISTOR

H03VV-F H03VVH2-F H05VV-F

H05VVH2-F A05VV-F



Popis	Ohybné šnúry
Menovité napätie	300/500 V
Typ	H03VV-F, H03VVH2-F, H05VV-F, H05VVH2-F, A05VV-F
Norma	EN 50525 2-11
Konštrukcia	Medené jadro ohybné IEC 60228 tr.5, PVC izolácia, PVC plášť
Farba	biela, čierna, šedá, oranžová
Príklad značenia	H05VV-F 4 G 0,75 300/500 V biela
Max. dovolená prevádzková teplota jadra	70°C
Odolnosť voči šíreniu plameňa	Podľa EN 60332-1
Bez obsahu olova	
Minimálna teplota pri inštalácii	-5°C
Použitie	V suchom prostredí pre nízke a stredné mechanické namáhanie k pohyblivým prívodom.
Polomer ohybu (min.)	4 D
Skúšobné napätie (AC)	2 kV

Počet žíl	x	Menovitý prierez jadra [mm ²]	Vonkajší priemer [mm]	Hmotnosť [kg/km]	Činný odpor jadra pri 20°C [ohm/km]	Obsah kovu (Cu) [Var.No./km]	Obvyklá dodacia dĺžka [m]
H03VH2-F 300/500 V							
2	x	0,5	5,0x3,1	27	39,0000	9,8	100 1000
2	x	0,75	5,4x3,3	33	26,0000	14,7	100 1000
2	x	0,75	6,2x4,0	41	26,0000	14,7	100 1000
2	x	1	6,8x4,3	50	19,5000	19,6	100 1000
H03VV-F 300/500 V							
2	x	0,5	4,9	36	39,0000	9,8	100 1000
2	x	0,75	5,3	44	26,0000	14,7	100 1000
3	x	0,5	5,2	43	39,0000	14,7	100 1000
3	x	0,75	5,7	53	26,0000	22	100 1000
4	x	0,5	5,7	51	39,0000	19,6	100 1000
4	x	0,75	6,2	65	26,0000	29	100 1000
H05VV-F 300/500 V							
2	x	0,75	6,1	55	26,0000	14,7	100 500
2	x	1	6,5	63	19,5000	19,6	100 500
2	x	1,5	7,4	84	13,3000	29	100 500
2	x	2,5	9,0	129	7,9800	49	100 500
2	x	4	10,3	176	4,9500	78	100 500
3	x	0,75	6,5	65	26,0000	22	100 500
3	x	1	6,9	75	19,5000	29	100 500
3	x	1,5	8,1	106	13,3000	44	100 500
3	x	2,5	9,8	162	7,9800	74	100 500
3	x	4	11,1	223	4,9500	118	100 500
4	x	0,75	7,1	78	26,0000	29	100 500
4	x	1	7,7	95	19,5000	39	100 500
4	x	1,5	9,0	133	13,3000	59	100 500
4	x	2,5	10,7	197	7,9800	98	100 500
4	x	4	12,2	277	4,9500	157	100 500
5	x	0,75	7,9	99	26,0000	37	100 500
5	x	1	8,4	116	19,5000	49	100 500
5	x	1,5	10,0	167	13,3000	74	100 500
5	x	2,5	11,9	247	7,9800	123	100 500
5	x	4	13,5	343	4,9500	196	100 500
A05VV-F 300/500 V							
2	x	6	11,5	235	3,3000	118	100 500
2	x	10	14,6	387	1,9100	196	100 500
3	x	6	12,7	304	3,3000	176	100 500
3	x	10	15,6	485	1,9100	294	100 500
4	x	6	13,8	379	3,3000	235	100 500
4	x	10	17,1	610	1,9100	392	100 500
5	x	6	15,2	462	3,3000	294	100 500
5	x	10	18,8	747	1,9100	490	50 500